1.1.3.5 Medium Power BeamTrack-Power / Position / Size Sensors

40mW to 150W

Features

- All the features of standard power sensors
- Accurate tracking of beam position to fractions of a mm
- Monitoring of the laser beam size









| Model Use | 50(150)A-BB-26-QUAD ^(a) General purpose | 50(150)A-BB-26-PPS (a) General purpose | F150A-BB-26-PPS (a) General purpose |
|--------------------------------------------------|-------------------------------------------------------|--------------------------------------------------|----------------------------------------|
| | | | |
| Absorber Type | Broadband | Broadband | Broadband |
| Spectral Range µm | 0.19 - 20 | 0.19 - 20 | 0.19 - 20 |
| Aperture mm | Ø26mm | Ø26mm | Ø26mm |
| Power Mode | | | |
| Power Range | 40mW - 150W | 40mW - 150W | 50mW - 150W (b) |
| Maximum Intermittent Power | 150W for 1.5min, 100W for 2.2min, 50W continuous | 150W for 1.5min, 100W for 2.2min, 50W continuous | N.A. |
| Power Scales | 150W / 50W / 5W | 150W / 50W / 5W | 150W / 30W / 3W |
| Power Noise Level | 2mW | 2mW | 8mW (b) |
| Maximum Average Power Density kW/cm ² | 12 at 150W, 17 at 50W | 12 at 150W, 17 at 50W | 12 at 150W, 17 at 50W |
| Response Time with Meter (0-95%) typ. s | 1.5 | 1.5 | 1.5 |
| Power Accuracy +/-% | 3 | 3 | 3 |
| Linearity with Power +/-% | 1.5 | 1.5 | 1 |
| Energy Mode | 1.5 | 1.5 | · |
| Energy Range | 20m J - 100 J | 20mJ - 100J | 20mJ - 100J |
| Energy Scales | 100J / 30J / 3J / 300mJ | 100J / 30J / 3J / 300mJ | 100J / 30J / 3J / 300mJ |
| Minimum Energy mJ | 20 | 20 | 20 (b) |
| Maximum Energy Density J/cm ² | 20 | 20 | 20 |
| <100ns | 0.3 | 0.3 | 0.3 |
| 0.5ms | 5 | 5 | 5 |
| 2ms | 10 | 10 | 10 |
| 10ms | 30 | 30 | 30 |
| Beam Tracking Mode | 30 | 30 | 30 |
| Position | | | |
| Beam Position Accuracy mm (c) | 0.1 | 0.1 | 0.1 |
| Beam Position Resolution mm | 2.5% of beam size | 2.5% of beam size | 2.5% of beam size |
| Min Power for Position Measurement | 1W | 1W | 1W |
| Size (d) | IVV | IVV | IVV |
| Size Accuracy mm (e) | N.A. | ±5% for centered beam | ±5% for centered beam |
| · · · · · · · · · · · · · · · · · · · | | | |
| Size Range mm (4σ beam diameter) | N.A. | Ø3 - 20 | Ø3 - 20 |
| Min Power Density for Size Measurement | N.A. | 1 W/cm ² | 1 W/cm ² |
| Cooling | convection | convection | fan |
| Fiber Adapter Available (see page 83) | ST, FC, SMA, SC | ST, FC, SMA, SC | ST, FC, SMA, SC |
| Weight Kg | 0.4 | 0.4 | 0.45 |
| Version | 770707 | 7707000 | 7707004 |
| Part number | 7Z07937 | 7 Z 07900 | 7Z07901 |

Notes: (a) The BeamTrack features are supported by StarBright, StarLite, Nova II and Vega meters, Juno and EA-1 interfaces and StarLab application.

Notes: (b) For powers up to 30W it is recommended to work with the fan off and then the noise level is \sim 3 times lower. It is also recommended to measure energy with the fan off.

Notes: (c) Position accuracy for the central 10mm of the aperture as limited by beam position resolution. Position can be tracked with ±1mm accuracy over the entire aperture. Accuracy is reduced by a factor of 3 at minimum power. Position measuring center corresponds to geometrical center within <1mm. Position center can be software reset to geometric center or other desired position with StarBright or StarLab.

Notes: (d) Assumes laser beam with Gaussian (TEM₀₀) distribution. For other modes, size measurement is relative.

Notes: (e) Accuracy spec will be maintained for beams from 3.5 to 17mm not deviating from center more than 15% of beam diameter. For beams below 8mm in size and powers above 75W error in size can reach ±10%.



